

$VersaCam^{\rm TM} \alpha$





THE ART OF EYE CARE



The Versatile, Portable **Fundus Imaging Unit**

The VersaCam^M α , designed specifically for the fundus imaging, provides high quality images with simple functionality. The lightweight and compact design allows easy portability from room to room or center to center, enhancing patient convenience. This portable unit with intuitive user functionality means fundus screenings can be performed virtually anywhere regardless of whether the patient is sitting or supine.







Clinics


Telemedicine

Education

High Quality Imaging



Normal



Age-related macular degeneration



clear-color camera with 45° horizontal angle of view (40° vertical) provides high quality digital imaging.

The 5-megapixel

Glaucoma

Excellent Portability



Lightweight and compact design

The VersaCam^m α is easily portable, weighing only 445 g including the ophthalmoscope adapter.



Rechargeable long lasting battery

A rechargeable lithium-ion battery provides up to 3 hours of continuous operation.



Handy carrying case

The carrying case designed exclusively for the VersaCamTM α is available for your convenience.

Easy Image Capture and Review



Auto focus

Auto focus and image capture can be performed with a single button for easy operation.



Internal fixation lamps

7 internal fixation lamps equipped with the VersaCam™ α allow stable fixation during measurement.



Color LCD touch screen

3.5-inch monitor allows easy review of the fundus images.



Peripheral devices (optional)

The VersaCam^M α can be attached to a slit lamp with a slit lamp attachment. A foot switch minimizes image blur due to hand movement during measurement.

Data Transfer and Management



Data from VersaCam^m α can be transferred to and managed by the NAVIS-EX, image filing software for NIDEK devices.

- DICOM connectivity
- Panorama photography

VersaCam[™] *α* Specifications

Туре	Non-mydriatic
Angle of view	45° (horizontal), 40° (vertical)
Camera resolution	5 megapixel CMOS
Minimum pupil diameter	ø3.5 mm
Focus range	-20 to +20 D
Focus	Auto, manual
Fixation	7 internal fixation lamps (LED)
Display	3.5-inch LCD touch screen
File format	JPEG (still image), H.264 (video)
Interface	Mini USB, AV out port
Memory	8 GB SD card
Power supply	Lithium-ion rechargeable battery
	AC 100 to 240 V
	50 / 60 Hz
Dimensions / Mass	
Main body	89 (W) x 40 (D) x 203 (H) mm / 285 g
	3.5 (W) x 1.6 (D) x 8 (H)" / 0.63 lbs.
Ophthalmoscope	118 (L) x 43 (Dia.) mm / 160 g
	4.6 (L) x 1.7 (Dia.)" / 0.35 lbs.
Charging station	56 (W) x 166 (D) x 106 (H) mm / 370 g
	2.2 (W) x 6.5 (D) x 4.2 (H)" / 0.82 lbs.
Optional accessories	External fixation lamp, foot switch, slit lamp attachment

Product / Model name: Digital Medical Scope DS-20 Specifications may vary depending on circumstances in each country. Specifications and design are subject to change without notice.



HEAD OFFICE (International Div.) 34-14 Maehama, Hiroishi Gamagori, Aichi 443-0038, JAPAN TEL: +81-533-67-8895 URL: http://www.nidek.com [Manufacturer]

TOKYO OFFICE (International Div.) 3F Sumitomo Fudosan Hongo Bldg., 3-22-5 Hongo, Bunkyo-ku, Tokyo 113-0033, JAPAN TEL: +81-3-5844-2641 URL: http://www.nidek.com

NIDEK S.A.

47651 Westinghouse Drive, Fremont, CA 94539, U.S.A. TEL: +1-510-226-5700 +1-800-223-9044 (US only) URL: http://usa.nidek.com

NIDEK INC.

Europarc, 13 rue Auguste Perret, 94042 Créteil, FRANCE TEL: +33-1-49 80 97 97 URL: http://www.nidek.fr

Via dell'Artigianato, 6/A, 35020 Albignasego (Padova),

ITALY TEL: +39 049 8629200/8626399 URL: http://www.nidektechnologies.it

#915, China Venturetech Plaza, 819 Nanjing West Rd, Jing An District, Shanghai 200041, CHINA TEL: +86 021-5212-7942 URL: http://www.nidek-china.cn

NIDEK TECHNOLOGIES S.R.L. NIDEK (SHANGHAI) CO., LTD. NIDEK SINGAPORE PTE. LTD. 51 Changi Business Park Central 2, #06-14, The Signature 486066, SINGAPORE TEL: +65 6588 0389

